

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-50-8033

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 3 Circuits



image - Reference only

Series

Documents:

- 3D Model

Packaging Specification PK-41695-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

41695

Application

Power, Wire-to-Board

MolexKits

Yes

Overview

KK® Interconnect System - Molex

Product Name

KK® 396

UPC

800753613799

Physical

Breakaway

No

Circuits (maximum)

3

Color - Resin

Natural

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

1.095/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm

Polarized to Mating Part

Yes

Temperature Range - Operating

See Product Specification

Material Info

Old Part Number

41695-N-D3

Reference - Drawing Numbers

Packaging Specification

PK-41695-001

Product Specification

PS-08-50

Sales Drawing

SD-41695

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
41695Series

Mates With
KK® 396 Header 41791 , 41792 , 41671 ,
41672 , 41661 , 41662

Use With
KK® 396 Crimp Terminals, 2478 , 2578 ,
6838 , 7258 , 45570

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION