



### Iron Adapter Kits

AC-FX1		Universal tip extraction iron adapter clip includes:
BTX-UC01	6	2 x universal clips
18574S-5	7	1 x silicon hose
DS03-910-5		1 x cleaning brush
20233S-5	8	1 x stainless tube
20237S-5		4 x S clips
18576S-5		1 x connecting gland

Other tip extraction iron adapter kits available:  
[www.okinternational.com/product\\_fume/btx\\_208](http://www.okinternational.com/product_fume/btx_208)

### Technical Specifications

Max. number of stations	8
Flow Rate per station	>28 l/min
Noise Level	< 55 db A
Dimensions (W x D x H)	508mm x 254mm x 388mm (20" x 10" x 15.3")
Weight	9kg (20lbs)
Voltage	100-240 VAC
Frequency	50-60 Hz
Power	85 Watt
Max Duct Run	30m (100')
Certification	UL/CSA/CE



## EC1800 Exhaust Cabinet



The EC1800 is an ideal bench top exhaust cabinet for applications such as volatile vapors and gases with high toxic levels.

A hinged and clear viewing panel maintains excellent visibility while at the same time reducing the airflow demand on the cabinet.

### Key Features & Benefits

- ▶ Bench Top exhaust cabinet
- ▶ Offers operators high levels of protection
- ▶ Easy Assembly
- ▶ Dimensions (W x D x H) 760 x 510 x 560mm (30" x 20" x 22")
- ▶ Connection Flange Ø100mm (4")
- ▶ Requires [MFX-2200G-A/D Gas Fume Filtration System \(page 29\)](#)

Part No.	Description
EC1800	Exhaust Cabinet with clear viewing panel
CH0047	Connection hose 2.5m (8') Long Ø100mm (4") with Clamps