



PRODUCT DATASHEET

Mirella series

last update 28/4/2014

DETAILS

Product Number	C13708_PF-SOCKET-VERO10
Family	Mirella
Type	Base part
Color	white
Diameter	38 mm
Height	3 mm
Style	round
Optic Material	
Holder Material	PC
Fastening	
Status	ready
ROHS Compliant	Yes
Date Updated	28/04/2014



OPTICAL PROPERTIES

LED	Viewing Angle	Light Beam	Efficiency	cd/lm	connector
VERO10	N/A degrees		-	(simulated) 0.000	-

4

3

2


1

D


C

B

A



Top view
without reflector



Isometric view
Scale: 3:2

LED position

Ø 49.9

Ø 31

C / C

Ø 3

4


3

2

1

CN13917_MIRELLA-50-S-PF-VER010
CN13919_MIRELLA-50-M-PF-VER010
CN13921_MIRELLA-50-W-PF-VER010

25.8




Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures:
Up to 30mm class F, otherwise class M.
According to DIN ISO 2768-2
Form and position: class K

LEDiL

Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

THIRD ANGLE PROJECTION:



DRAWING TITLE

MIRELLA-50-PF-VER010

This drawing is the property
of LEDiL Oy. It may not be
reproduced, copied or
communicated without a written
agreement with LEDiL Oy."

SIZE

A4

PART NUMBER

-

SCALE

3:2

WEIGHT

-

SHEET

1 / 1

D

A

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

GENERAL INFORMATION

- Product series especially designed & optimized for series of LEDs.
- Special care taken to make light distribution as uniform as possible.

Note! Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.