



Code No. Eyewash 250ml/500ml/20ml
Page 1 / 3

Dated 30.05.2012
Version 1.0

Sterile Eyewash Solution (Sodium Chloride 0.9%)

PRODUCT AND COMPANY INFORMATION – SECTION 1

Manufacturer :	Safety First Aid Group Ltd
	15-17 The Garrick Centre, Irving Way, London NW9 6AQ, UK
	Tel.: +44 (0)20 8202 7447
	Fax.: +44 (0)20 8203 9077
Product Name:	Sterile Eyewash Solution (Sodium Chloride 0.9%)
Synonyms:	-----
Intended Use:	A sterile solution for eye irrigation and not for injection.

EMERGENCY CONTACT

Tel.: +44 (0)20 8202 7447
Fax.: +44 (0)20 8203 9077

HAZARDOUS INGREDIENTS – SECTION 2

Sterile Eyewash Solution (Sodium Chloride 0.9%) does not contain hazardous ingredients. Contains sodium chloride (Eur. Pharm.) 0.9% in water for injections. It does not contain a preservative.

HAZARDOUS IDENTIFICATION – SECTION 3

This is nonflammable aqueous solution

EMERGENCY OVERVIEW

When used according to instructions, the product applicable to this MSDS is stable and safe and presents no immediate or long - term health hazard. However if you feel anything unusual during or after Sterile Eyewash Solution (Sodium Chloride 0.9%) has been used, call for immediate medical attention.



Code No. Eyewash 250ml/500ml/20ml
Page 2 / 3

Dated 30.05.2012
Version 1.0

Sterile Eyewash Solution (Sodium Chloride 0.9%)

FIRST AID MEASURES – SECTION 4

FIRST AID MEASURES

Eye Contact :

Not applicable

Skin contact :

Not applicable

Inhalation:

Not applicable

Ingestion:

Not applicable

FIRE AND EXPLOSION DATA – SECTION 5

Flammability of the product

Non - flammable

Auto - Ignition Temperature

Not applicable

Flash Points

Not applicable

Flammable limits

Not applicable

Products of Combustion

Not available

Fire Hazards in Presence of Various Substances

Not applicable

Explosion Hazards in Presence of Various Substances

Non - explosive in presence of open flames and sparks

Fire Fighting Media and instructions

Not applicable

Special Remarks on Fire Hazards

Not available

ACCIDENTAL RELEASE MEASURES - SECTION 6

Flush area with water. The solution is not RCRA hazardous waste

HANDLING AND STORAGE - SECTION 7

Do not freeze or expose to temperatures in excess of 25 °C (86 °F)

EXPOSURE CONTROLS / PERSONAL PROTECTION - SECTION 8

Eye Protection:

None required

Skin Protection:

None required

Respiratory Protection:

None required

Ventilation:

None required

Protecting clothing or equipment:

None required



Code No. Eyewash 250ml/500ml/20ml
Page 3 / 3

Dated 30.05.2012
Version 1.0

Sterile Eyewash Solution (Sodium Chloride 0.9%)

PHYSICAL & CHEMICAL PROPERTIES - SECTION 9

General Information:

Appearance:	Colorless Liquid
Odor:	Not available
Boiling Point :	The lowest known value is 100 °C (212 °F)
Solubility In Water:	100%

STABILITY & REACTIVITY - SECTION 10

Stability:

This product is stable and considered non-reactive under normal conditions of storage and usage

TOXICOLOGICAL INFORMATION - SECTION 11

No acute or chronic toxic effects expected when used according to directions

ECOLOGICAL INFORMATION - SECTION 12

No ecological or special consideration when used according to directions. This product is not considered environmentally harmful from normal dilution, expected usage and typical drainage to sewers, septic systems and treatment plants.

DISPOSAL CONSIDERATION - SECTION 13

N/A

TRANSPORT INFORMATION - SECTION 14

N/A

REGULATORY INFORMATION - SECTION 15

N/A

OTHER INFORMATION - SECTION 16

Revision Number	Revision Date
1	30.05.2012

To the best of our knowledge, the information containing herein is accurate. However, neither SFAG nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information containing herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.