



EMPTY ENCLOSURE

TK PS 1111-7-m



TK PS 1111-7-m

Empty enclosure

CUSTOMIZABLE

110 x 110 x 66 mm
Article number: 10540401

Empty enclosure, base and cover: polystyrene, grey, similar to RAL 7035

with metric knockouts



Technical data

Measures

| | |
|---------------|--------|
| Width: | 110 mm |
| Length: | 110 mm |
| Height: | 66 mm |
| Inner height: | 53 mm |

Material

| | |
|--------------|--|
| Base: | Polystyrene, grey, similar to RAL 7035 |
| Cover: | Polystyrene, grey, similar to RAL 7035 |
| Sealing: | Polyurethane |
| Cover screw: | Polyamide 6, fiber-glass reinforced |

Accessory

ASS-kl - External hinge set

HBA - Mounting material

MPS-KRI - Mounting plate

NS 35-81 - Mounting rail

TK DST - Spacing kit

TK MPI-1111 - Mounting plate

TS 15-92 - Mounting rail

Environmental attributes

| | |
|--|--------|
| Ambient temperature (min.): | -25 °C |
| Ambient temperature (max.): | 40 °C |
| Ambient temperature (24 h): | 35 °C |
| Max. rel. humidity at 25° C (short Therm): | 95% |
| Max. rel. humidity at 40° C: | 50% |



EMPTY ENCLOSURE

TK PS 1111-7-m

Other attributes

| | |
|---------------------------------|---|
| Ingress protection: | IP66 - acc. EN 60529 / DIN VDE 0470-1 |
| Impact resistance: | IK07 acc. DIN EN 5012 / VDE 0470 Part 100 |
| Protection class: | II - isolate protection acc. VDE 0106 |
| Rated insulation voltage AC: | 690V V |
| Rated insulation voltage DC: | 1000 V |
| Heavy metals-free: | Yes |
| PVC-free: | Yes |
| Silicone-free: | Yes |
| Fitted for outdoor application: | No |
| Combustion behaviour to UL: | HB acc. UL94 |
| Combustion behaviour to VDE: | 650°C acc. VDE 0471/ EN 60695 |
| sealable: | Yes |
| Weatherproof: | No |
| Knockouts: | Yes |