

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-55-2042

Status:

Active

Overview:

SL™ Modular Connectors

Description:

2.54mm Pitch SL™ Crimp Housing, Dual Row, Version B, Polarized, 4 Circuits



Series

image - Reference only

Documents:

- 3D Model

Product Specification PS-70400 (PDF)
- Drawing (PDF)

Test Summary TS-70058-001 (PDF)
- Product Specification PS-70058 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

70450

Application

Signal, Wire-to-Board

Comments

Version B

Overview

SL™ Modular Connectors

Product Name

SL™

UPC

800754395748

Physical

Breakaway

No

Circuits (maximum)

4

Color - Resin

Black

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Material - Resin

Polyester

Net Weight

0.370/g

Number of Rows

2

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Material Info

Old Part Number

704500050

Reference - Drawing Numbers

Product Specification

PS-70058, PS-70400

Sales Drawing

SD-70450-0050-0075

Test Summary

TS-70058-001

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

70450Series

Mates With

2.54mm Pitch C-Grid® Header [70229](#) ,
[70280](#) , [70246](#) , [70247](#)

Use With

[70058](#) , [71851](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION