

## **10 ft DisplayPort to DVI Video Adapter Converter Cable - M/M**

*StarTech ID: DP2DVIMM10*



The DP2DVIMM10 DisplayPort to DVI (M-M) Video Converter Cable lets you connect a DVI capable display to a DisplayPort video card/source using a single cable. The cable provides a connection distance of 10ft and features a male DVI connector and a male DisplayPort connector.

The DisplayPort/DVI video converter cable supports high bandwidth video transmissions, easily delivering monitor resolutions up to 1920x1200 or HDTV resolutions up to 1080p - allowing you to take full advantage of your DVI capable display, while using a cutting edge DisplayPort video source.

DP2DVIMM10 is a passive adapter cable that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Applications**

- Keep your existing DVI display with our DisplayPort to DVI video converter cables
- The DisplayPort to DVI cable allows for an easy and hassle free connection to any DVI-D (digital) display

### **Features**

- Supports PC resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Easy to use cable, no software required

## Technical Specifications

Warranty	2 Years
Converter Type	Passive
Adapter Style	Cable Adapter
Audio	No
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector A	1 - DisplayPort (20 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Maximum Cable Length	3 m [10 ft]
Maximum Digital Resolutions	1920x1200 / 1080p
<b>Note</b>	DP++ (DisplayPort++) port required from video card or video source.
Color	Black
Cable Length	3 m [10 ft]
Product Length	3048 mm [120 in]
Product Weight	0.1 kg [0.2 lb]
Shipping (Package) Weight	0.1 kg [0.2 lb]
Included in Package	1 - 10 ft DisplayPort to DVI Video Adapter Converter Cable - M/M

## Certifications, Reports and Compatibility

