



MMF



MHFML195C



GMHFML195C



MLFML195C



MHFPP240C



GMLFML195C



MTPMHF



MVPHF

High Frequency Mounts

3/4" hole; 1-1/8"-18 thread; Crimp on

Model	Mount Type	Coax	Connector
MMF	Permanent microwave mount for frequencies from 800 MHz to 3.0 GHz for up to .06" thick roof surfaces.	None	Male SMA*
MMF-VP	Permanent mount for frequencies from 0 GHz to 6 GHz.	None	Male SMA
MHFML195C**	Permanent microwave mount for frequencies from 3.0 GHz to 5.8 GHz for up to 0.046" thick roof surfaces	17 ft. Pro-Flex™ Plus 195	Loose TNC male standard. Other connector options (NF, NM, RPC) are available.
GMHFML195C**	Magnetic base microwave mount for frequencies from 3.0 GHz	12 ft. Pro-Flex™ Plus 195	Attached TNC male standard. Contact customer service for other connector options.
MLFML195C	Permanent mount for frequencies from 800 MHz to 3.0 GHz for up to 0.046" thick roof surfaces	17 ft. Pro-Flex™ Plus 195	Loose TNC male standard. Contact customer service for other connector options.
MHFPP240C**	Permanent mount for frequencies from 800 MHz to 3.0 GHz for up to 0.046" thick roof surfaces	17 ft. Pro-Flex™ Plus 240	Loose TNC male standard. Contact customer service for other connector options.
GMHFPP240C**	Magnetic mount for frequencies from 800 MHz to 3.0 GHz for up to 0.046" thick roof surfaces	12 ft. Pro-Flex™ Plus 240	Attached TNC male standard. Contact customer service for other connector options.
GMLFML195C	Magnetic base mount for frequencies from 800 MHz to 3.0 GHz	12 ft. Pro-Flex™ Plus 195	Attached TNC male standard. Contact customer service for other connector options.
MLFPP240C	Permanent mount for frequencies from 800 MHz to 3.0 GHz for up to 0.046" thick roof surfaces	17 ft. Pro-Flex™ Plus 240	Loose TNC male standard. Contact customer service for other connector options.

High Frequency Mounts For Thick Roof Surfaces

5/8" hole; 1-1/8"-18 thread; Crimp on

Model	Mount Type	Coax	Connector
MTPMHF**	Permanent microwave mount for use with MLPV4900NGP, MEFC49005HF, or MEFC58005HF high frequency antennas. For surfaces up to 1-inch thick.	None	N Female* connector
MVPHF**	Vandal-proof microwave mount for use with MLPV4900NGP, MEFC49005HF, or MEFC58005HF high frequency antennas. For surfaces up to 1/2-inch thick.	None	M to N Female* connector
MVPHF	Vandal-proof permanent mount for frequencies from 900 MHz to 6 GHz. Accommodates surfaces up to 1/2-inch thick.	None	M to N Female*

* Cable assembly with mating connector sold separately.

** High frequency mount to be used with (B)MEFC49005HF, (B)MEFC58005HF, MEFC2327HF and MLPV4900NGP.

