

CRIMPER 1600 FERRULES AWG 20-12



Cat No: PA1648 UPC No: 769328100778

Description

- Professional crimping tool for insulated and non-insulated wire ferrules with a range of 20-12 AWG (0.5-4 mm²)
- Fixed steel die system
- Ferrules insert from side of the tool
- Ferrule crimp conforms to DIN standards
- Durable steel construction for long life
- Ergonomic handles for low-effort operation
- Single tool for entire wire range

Specifications

- Application : For Insulated And Non-Insulated Wire Ferrules With A Range Of 20-12 AWG (0.500 - 4.000 SQ-MM)
- Crimping Range : 20-12 AWG
- Handle Type : Ergonomic
- Material : Durable Steel
- Standard : DIN
- Type : Wire Ferrule
- Weight : 15.200 OZ (430.000 GM)