



- Impeller are UL 94V-0 rating
- Impedance protected
- Leader wire or Terminal is available

**OPERATING TEMPERATURE :**

- Ball bearing - 30°C to +75°C
- Sleeve bearing - 10°C to +70°C

**WEIGHT :**

330 grams

**Specifications**

Specifications are subject to change without notice

MODEL NO.	BEARING	RATED VOLTAGE	FREQUENCY	MAX. RATED CURRENT	MAX. INPUT POWER	SPEED	MAX. AIR FLOW		MAX. AIR PRESSURE		NOISE
		VAC	Hz	mA	W	R.P.M.	m <sup>3</sup> /min	CFM	mmH <sub>2</sub> O	IN H <sub>2</sub> O	
12P-115LB	Ball	115	50/60	150/130	14/13	1600±15% /2000	1.3/1.5	46.3/52.7	1.9/2.1	0.1/0.1	29/34
12P-115LS	Sleeve										
12P-115HB	Ball	115	50/60	170/150	16/14	2000/2400	1.6/1.7	55.0/60.4	2.7/2.5	0.1/0.1	39/42
12P-115HS	Sleeve										
12P-230LB	Ball	230	50/60	90/80	18/16	1600/2000	1.3/1.5	46.3/52.7	1.9/2.1	0.1/0.1	29/34
12P-230LS	Sleeve										
12P-230HB	Ball	230	50/60	95/85	18/16	2200/2600	1.6/1.7	55.0/60.4	2.7/2.5	0.1/0.1	39/42
12P-230HS	Sleeve										

