

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [22-01-3167](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Housing, Friction Ramp, 16 Circuits](#)

Documents:
[3D Model](#) [Packaging Specification PK-2695-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [2695](#)
Application Signal, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name KK® 254
UPC 800753690141

Physical

Circuits (maximum) 16
Color - Resin Natural (White)
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 1.690/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating See Product Specification

Material Info

Old Part Number 2695-16RP

Reference - Drawing Numbers

Packaging Specification PK-2695-001
Product Specification PS-10-07
Sales Drawing SD-2695



image - Reference only Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[2695Series](#)

Mates With
KK®254 PCB Headers [42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With
[2759](#) , [4809](#) KK® Crimp terminal