

NOTES:


1. ROHS COMPLIANT
2. MATERIALS:
FIBER OPTIC: Ø1.5MM OPTICAL CORE, Ø2.2MM POLYETHYLENE CABLE JACKET
LENS MOUNT: OPTICAL GRADE ACRYLIC
LED MOUNTS: FOR SMD 22 & THR 22 - NYLON 66, UL RATING 94-V2
FOR THR 5 22 - NYLON 66, UL RATING 94-HB
LENS: POLYCARBONATE, UL RATING 94-V2
LENS SPACER: POLYPROPYLENE
3. OPTICAL CORE ENDS POLISHED TO 10 MICRONS
4. PANEL MOUNTING HOLE: .171"±.002 (4.34mm±0.05) ON 1/4"(6.35mm) CENTERS
5. PANEL THICKNESS FOR SML 190: 1/32" (0.79mm) TO 1/16"(1.60mm);
SMB 200 AND SMQ 250: 1/16" (1.60mm) TO 1/8" (3.48mm)
6. FOR ADDED SECURITY FOR SMB 200 AND SMQ 250 USE SPC 040 SPACER
7. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED
LEDS WITH OUTPUT POWER GREATER THAN 100mcd
8. U.S. AND FOREIGN PATENTS ISSUED

LITE PIPE ASSEMBLY
ORDERING CODE (EXAMPLE): **FLX3 XX**


LENGTH	
LENGTH CODE	ACTUAL LENGTH
02	2.0"
04	4.0"
06	6.0"
08	8.0"
12	12.0"
CUSTOM LENGTHS AVAILABLE UPON REQUEST	

REVISIONS					
ECN #	REV.	DESCRIPTION	DATE	INITIALS	CHK'D
-	001	INITIAL RELEASE	2/4/10	KH	AZ
-	002	MOD TO NOTE 4&5; CHG Ø.059 TO Ø.039	7/20/10	KH	AZ
-	003	REVISED PER ECR 092810AA01	10/4/10	KH	AZ
397	004	REVISED PER ECR 011812KH01	1/19/12	KH	AZ


MOUNTING OPTIONS (ORDER SEPARATELY)




SMD 22




THR 22




THR 5 22




LENS (ORDER SEPARATELY)



SMB 200



SML 190



SMQ 250

DIMENSION STYLE: INCHES / MM GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	 OPTOELECTRONICS 190 BOSSTICK BLVD, SUITE 101 SAN MARCOS, CA 92069 U.S.A. PHONE: (760) 560-1300, FAX: (760) 560-1301 EMAIL: vccsales@vccsite.com
INCHES	MM	DRAWN	KHOWARD	2/4/10	
X ± .020 ± .508		CHECKED	AZANELLI	2/10/10	
XX ± .010 ± .254					
XXX ± .005 ± .127					
ANGLE 1°		MATERIAL		TITLE:	
 THIRD ANGLE PROJECTION		SEE NOTES		3MM FLEXFIRE FLEXIBLE LITEPIPE	
PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VISUAL COMMUNICATIONS COMPANY, INC IS PROHIBITED.		FINISH		SIZE B	DWG. NO. FLX3 XX
DO NOT SCALE DRAWING		SCALE: 2:1		REV 004	SHEET 1 OF 2