

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINDICHT® O-Ring Perbunan® metric	14.11.2013



UV-resistant

Application range

For sealing the housing reliably to protect against oils, dust, and water at the connection thread of a gland or other similar parts

Note

O-rings with thickness of 1.5 mm are recommended for optimum sealing of the converter SKINDICHT® ZSE-M12/16/20 x 1.5
Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Remark

Perbunan® is a registered trademark of BAYER AG

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Colour delivered:	Black
Material:	NBR Ozone and UV-resistant silicone-free
Temperature range:	-30°C to +100°C

Product Management	Document: LAPP_PRO102476EN.pdf	1 / 2
--------------------	--------------------------------	-------



SKINDICHT® O-Ring Perbunan® metric

14.11.2013

Part number	Article designation / size	Inner Ø (mm)	Cable thickness (mm)	Pieces / PU
SKINDICHT® O-Ring Perbunan®				
53102001	O M 12 x 1,5	9.0	1.5	100
53102000	O M 12 x 2,0	9.0	2.0	100
53102010	O M 16 x 2,0	13.0	2.0	100
53102021	O M 20 x 1,5	17.0	1.5	100
53102020	O M 20 x 2,0	17.0	2.0	100
53102030	O M 25 x 2,0	22.0	2.0	100
53102040	O M 32 x 2,0	28.0	2.0	50
53102050	O M 40 x 2,0	36.0	2.0	50
53102060	O M 50 x 2,0	46.0	2.0	25
53102070	O M 63 x 2,0	57.0	2.0	25