

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19006-0017

Status:

Active

Overview:

Quick-Disconnect Terminals

Description:

Flag Avikrimp™ Quick Disconnect, Female, for 14-16 (2.00-1.30mm²) Wire, Box, Tab 4.75 x 0.81mm

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

Product Specification PS-19902-014 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19006

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Quick-Disconnect Terminals

Product Name

Avikrimp™

Type

Quick Disconnect

UPC

800753031166

Physical

Barrel Type

Closed

Color - Resin

Blue

Flammability

94V-2

Gender

Female

Glow-Wire Compliant

Yes

Insulation

Nylon (PA)

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

1.374/g

Orientation

Flag

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

4.75mm

Temperature Range - Operating

-65°C to +105°C

Wire Insulation Diameter

4.32mm max.

Wire Size AWG

14, 16

Wire Size mm²

1.30 - 2.00

Electrical

Voltage - Maximum

600V

Material Info

Old Part Number

BB-5225

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013, PS-19902-014

Sales Drawing

CDFLA187



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19006Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640014300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640054300

This document was generated on 10/14/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION