

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>19154-0030</u>
Status:	Active
Overview:	Splices
Description:	InsulKrimp™ Butt Splice for 10-12 AWG Wire, Tape and Reel

Documents:

Drawing (PDF)	Product Specification PS-19902-015 (PDF)
Product Specification PS-19902-007 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011 (PDF)	

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	<u>19154</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>Splices</u>
Product Name	Butt, InsulKrimp™
UPC	800753108967

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Insulation	PVC
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	2.387/g
Packaging Type	Adhesive Tape on Reel
Wire Size AWG	10, 12

Material Info

Old Part Number C-246XT

Reference - Drawing Numbers

Product Specification	PS-19902-007, PS-19902-011, PS-19902-015
Sales Drawing	SD-19154-006



image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen



China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, click [here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19154Series

Application Tooling | FAO

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	<u>0192880179</u>
Mini-Mac™ Applicator	<u>0638851500</u>

This document was generated on 10/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION