

# REGAL WEALTH ENGINEERING LIMITED

ADD: SUZHOU REPRESENTATIVE OFFICE, 0203A1 1A SINGA PLAZA JINJIHU ROAD SUZHOU  
INDUSTRIAL PARK, P.R.CHINA

TEL: 86-512-62532393

FAX:86-512-62532690

## Technical Data Sheet

**Mode Number: CB17774**

**File Number: 2014-10-29-001**

- |                                     |   |
|-------------------------------------|---|
| <b>1. Name of cable:</b>            | <b>Speaker Cable</b>                        |
| <b>2. P/N:</b>                      | <b>17774 2X7/0.20mm CCA</b>                 |
| <b>3. Designed of cable:</b>        |   |
| <b>3.1 Inner conductor:</b>         | <b>7/0.20±0.005mm Strand CCA Ø0.6±0.1mm</b> |
| <b>4. Jacket:</b>                   | <b>PVC</b>                                  |
| <b>4.1 Colour:</b>                  | <b>White with black trip</b>                |
| <b>4.2 Size:</b>                    | <b>Ø2X4±0.2mm</b>                           |
| <b>4.3 Wall thickness:</b>          | <b>≈0.7 mm</b>                              |
| <b>4.4 Printing:</b>                | <b>By request bargain</b>                   |
| <b>5. Electric data at 20°C:</b>    |   |
| <b>5.1 Conductor resistance:</b>    | <b>≤145.0Ohm/KM</b>                         |
| <b>5.2 Insulation resistance:</b>   | <b>≥200M ohm*KM</b>                         |
| <b>5.3 Testing voltage:</b>         | <b>wire/wire 50Hz1min=800V</b>              |
| <b>6. Other requirement:</b>        |   |
| <b>6.1 Permissible temperature:</b> | <b>-10°C----60°C</b>                        |
| <b>6.2 Packing:</b>                 | <b>100M On non-returnable reel</b>          |
| <b>6.3 Test standard:</b>           | <b>This Technical Data Sheet</b>            |

Designed by Regal Wealth Engineering Ltd

2014.10.29