



# Einhell

**EXPERT Plus**

## TE-OS 18 Li - Solo Cordless Multiple Sander

The TE-OS 18 Li – Solo cordless multi sander is a compact and handy sander from Power X-Change family of devices which combines the best ergonomics with maximum functionality for lending surfaces a good finish. The ergonomic grip area with Softgrip is good to hold. Experts appreciate the tool as an indispensable helper which really demonstrates its strengths particularly on small and hard-to-reach surfaces. The tool is supplied without battery and charger but it can be powered by Power X-Change rechargeable batteries.

### Features

- Member of the Power X-Change family
- Grip area with softgrip modeled on the palm of a hand
- Small, compact and easy to handle
- Flexible in use for sanding corners and small surfaces
- “Extreme Fix” Velcro fastening for quick change of abrasive paper
- High removal rate with “Extreme Fix” due to reduced slippage
- Solid, rugged aluminium fan impeller for smooth running
- Active dust extraction keeps the work area clean
- Filter box collects dust from grinding/sanding
- Incl. vacuum cleaner adapter for even more cleanliness
- Complete with six sheets of abrasive paper for wood
- Supplied without battery and charger (available separately)



### Technical Data

- |                         |                          |
|-------------------------|--------------------------|
| • Accumulator           | 18 V   Lilo              |
| • Idle speed            | 12.000 min <sup>-1</sup> |
| • Oscillations          | 24.000 min <sup>-1</sup> |
| • Sanding paper size    | 93 x 60 x 105 mm         |
| • Oscillating circuit Ø | 1,6 mm                   |



### Logistic Data

- |                               |                    |
|-------------------------------|--------------------|
| • Dimensions single packaging | 245 x 120 x 145 mm |
| • Dimensions Export Carton    | 600 x 500 x 190 mm |



Illustrations can contain accessories, which are not included in standard extent of delivery  
 Illustration similar (in design), production-wise modifications reserved  
 GS mark belongs to the product itself only, excluded accessory