

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39-00-0059

Status:

Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel



image - Reference only

Series

Documents:

- Drawing (PDF)

Product Specification PS-51010-003 (PDF)

Product Specification PS-51010-004 (PDF)

Product Specification PS-51045-003 (PDF)

Product Specification PS-52252-001 (PDF)

Product Specification PS-54849-004 (PDF)
- Product Specification PS-5556-001 (PDF)

Product Specification PS-5556-002 (PDF)

Packaging Specification PK-5556-001 (PDF)

Test Summary TS-5556-002 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0060 (Loose)
Product Name	Mini-Fit®
UPC	800753584662

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.127/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5556PBT
-----------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-51010-003, PS-51010-004, PS-51045-003, PS-52252-001, PS-54849-004, PS-5556-001, PS-5556-002, RPS-501566-001, RPS-51010-013, RPS-51045-002, RPS-54269-004, RPS-5557-001, RPS-5557-004, RPS-5557-027, RPS-5557-034, RPS-5557-035, RPS-5557-044, RPS-5557-045, RPS-5557-048, RPS-5557-049, RPS-5557-054
Sales Drawing	SD-5556****
Test Summary	TS-5556-002

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5556Series

Mates With

5558 Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, 5566 , 5569

Use With

5557 Mini-Fit Jr.™ Receptacle Housing, 30067 Mini-Fit® TPA, 42474 Mini-Fit® BMI Panel Mount, 5559 Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900

T2 Terminator™ for 0639102900
insulation OD 1.65
– 2.05mm – 18 – 24
AWG
FineAdjust™ 0639023900
Applicator for
Insulation OD
1.40-1.70mm - 18-24
AWG
T2 Terminator™ 0639115600
for insulation OD
1.90-2.30mm - 18-24
AWG
T2 Terminator™ 0639123900
for insulation OD
1.40-1.70mm - 18-24
AWG
FineAdjust™ 0639002600
Applicator for
Insulation OD
2.50-2.95mm - 18-24
AWG
FineAdjust™ 0639002900
Applicator for
Insulation OD
1.65-2.05mm - 18-24
AWG
FineAdjust™ 0639024900
Applicator for
Insulation OD
2.30-2.60mm - 18-24
AWG
T2 Terminator™ 0639124900
for insulation OD
2.30-2.60mm - 18-24
AWG
T2 Terminator™ 0639102600
for insulation OD
2.50-2.95mm - 18-24
AWG
FineAdjust™ 0639015600
Applicator for
Insulation OD
1.90-2.30mm - 18-24
AWG
FineAdjust™ 0639024800
Applicator for
Insulation OD
2.50-2.95mm
Optimized for 18
AWG Only
T2 Terminator™ 0639124800
for insulation OD
2.50-2.95mm
optimized for 18
AWG only
Extraction Tool 0011030044

Japan	
Description	Product #
Applicator for M211A Bench Press, 18-24	0570223000
AWG Wire	
Side-Feed Applicator For Full-Auto Machine	0570223200

This document was generated on 10/06/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION