

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-50-8061

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 6 Circuits



image - Reference only

Series

Documents:

3D Model

Drawing (PDF)

Product Specification PS-08-50 (PDF)

Packaging Specification PK-41695-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	41695
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 396
UPC	800754227742

Physical

Breakaway	No
Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	2.105/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Material Info

Old Part Number	41695-N-B6
-----------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-41695-001
Product Specification	PS-08-50
Sales Drawing	SD-41695

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

41695Series

Mates With

KK® 396 Header [41791](#) , [41792](#) , [41671](#) , [41672](#) , [41661](#) , [41662](#)

Use With

KK® 396 Crimp Terminals, [2478](#) , [2578](#) , [6838](#) , [7258](#) , [45570](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION