

# EATON - AE16BNS0CC

## Non-Reversing Starter Interchangeable Heater 480/440V 60/50Hz 10A I.E.C. Size B

EATON

### Product Description

Magnetic Starter: Type - Non-Reversing Starter; Construction Standard - I.E.C. 600V AC; Size - I.E.C. Size B; UL Cont. Amps - 10A; Phase - 3PH; Coil Voltage - 480/440V 60/50Hz; Hp 1-Phase 115V - 0.5 Hp; Hp 1-Phase 230V - 1 Hp; Hp 3-Phase 200V - 2 Hp; Hp 3-Phase 230V - 2 Hp; Hp 3-Phase 460V - 5 Hp; Hp 3-Phase 575V - 7.5 Hp; Enclosure Type - Open; Overload Relay - Interchangeable Heater; Motor FLA - Refer to Heater; Auxiliary Contacts - 1 NO Side Mounted; Manufacturer Series - Freedom

Type:	Non-Reversing Starter
Construction Standard:	I.E.C. 600V AC
Size:	I.E.C. Size B
UL Cont. Amps:	10A
Phase:	3PH
Coil Voltage:	480/440V 60/50Hz
Hp 1-Phase 115V:	0.5 Hp
Hp 1-Phase 230V:	1 Hp
Hp 3-Phase 200V:	2 Hp
Hp 3-Phase 230V:	2 Hp
Hp 3-Phase 460V:	5 Hp
Hp 3-Phase 575V:	7.5 Hp
Enclosure Type:	Open
Overload Relay:	Interchangeable Heater
Motor FLA:	Refer to Heater
Auxiliary Contacts:	1 NO Side Mounted
Manufacturer Series:	Freedom