



PIN OUT

AM ——— BM

- 1 ————— 1
- 2 ————— 2
- 3 ————— 3
- 4 ————— 4
- 5 ————— 5
- 6 ————— 6
- 7 ————— 7
- 8 ————— 8
- 9 ————— 9

SHELL (BRAID+DRAIN) SHELL



- NOTES:
- MATERIALS
 - CABLE: (7/0. 12BC*1P+7/0. 12BC+FAM)*2PCS+7/0. 20TC*2C+7/0. 12TC*1P+AM+7/0. 12TC+128/0. 12ALM+WHITE (4010) PVC JACKET
OD=∅5.5 ± 0.15MM.
 - CABLE PRINTING: USB 3.0 SUPER SPEED CABLE
 - P1: USB 3.0 A TYPE MALE: SOLDER TYPE, BLUE PBT INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
 - P2: USB 3.0 B TYPE MALE: SOLDER TYPE, BLUE PBT INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
 - ALL HOOD: MOLDED WHITE (4010) PVC PVC.
 - TESTING: 100% OPEN AND SHORT TEST.
 - PACKING: 1PC/PE BAG.
 - ALL MATERIAL BE ROHS COMPLIANT.

REV. 00		FROM CS14579 TO CS28250		2014-11-13		LENGTH TOLERANCE: X: ± 0.5 .X ± 0.2 .XX ± 0.1		SCALE: FREE		CUS. NAME: CPC		PRODUCT NO: 1060		CUSTOMER NO: CS28250		ENG: Mr. Zhang	
ECN.		MODIFY DESCRIPTION		DATE		ANGLE TOLERANCE: X: ± 3° .X: ± 1°		UNIT: mm		PAGE: 1/1		DRAWING NO: 1060		PRODUCT DESCRIPTION: USB3.0 AM/BM		APPROVED:	
1		2		3		4		5		6		7					