

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

08-52-0125

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® Trifurcon™ Crimp Terminal 7258, 22-26 AWG, Bag, Phosphor Bronze Tin (Sn)

Documents:

Drawing (PDF)

Product Specification PS-40-02 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Packaging Alternative

Product Name

UPC

Crimp Terminals

7258

Power

Yes

KK® Interconnect System - Molex

08-52-0124 (Reel)

KK®, Trifurcon™

800753756694

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

Phosphor Bronze

Tin

Tin

0.159/g

Bag

2.540µm

2.540µm

Crimp or Compression

1.65mm max.

22, 24, 26

N/A

Material Info

Old Part Number

7258-A(P909)L

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-40-02

SD-7258



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7258Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for	0638117400
Crimp Terminals	
Extraction Tool	0011030016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION