

## Low Smoke BW & CW Gland Kits

### Product Type:

Low Smoke BW & CW Gland Kits

### Standards:

CW are waterproof to standards IP66 on inner and outer seal  
Manufactured to BS6121 Part 1

### Application:

BW and CW cable glands, suitable for securing most rubber and plastic coated cables to electrical sources. The cables come complete with a locking nut offering positive armour locking and effective earth continuity. Can be used in corrosive conditions when used with shroud. The shrouds are low smoke fume.



### Low Smoke BW Gland Kits

Code	Description	Pack Qty
ABW20S-LSF	Brass cbl gld 20mm 2 Pt Kt	2
ABW20-LSF	Brass cbl gld 20mm 2 Pt Kt	2
ABW25-LSF	Brass cbl gld 25mm 2 Pt Kt	2
ABW32-LSF	Brass cbl gld 32mm 2 Pt Kt	2
ABW40-LSF	Brass cbl gld 40mm 2 Pt Kt	1
ABW50S-LSF	Brass cbl gld 50mm 2 Pt Kt	1
ABW50-LSF	Brass cbl gld 50mm 2 Pt Kt	1
ABW63S-LSF	Brass cbl gld 63mm 2 Pt Kt	1
ABW63-LSF	Brass cbl gld 63mm 2 Pt Kt	1
ABW75S-LSF	Brass cbl gld 75mm 1 Pt Kt	1
ABW75-LSF	Brass cbl gld 75mm 1 Pt Kt	1

## Low Smoke CW Gland Kits

Code	Description	Pack Qty
ACW20S-LSF	Brass cbl gld 20mm 2 Pt Kt	2
ACW20-LSF	Brass cbl gld 20mm 2 Pt Kt	2
ACW25-LSF	Brass cbl gld 25mm 2 Pt Kt	2
ACW32-LSF	Brass cbl gld 32mm 2 Pt Kt	2
ACW40-LSF	Brass cbl gld 40mm 1 Pt Kt	1
ACW50S-LSF	Brass cbl gld 50mm 1 Pt Kt	1
ACW50-LSF	Brass cbl gld 50mm 1 Pt Kt	1
ACW63S-LSF	Brass cbl gld 63mm 1 Pt Kt	1
ACW63-LSF	Brass cbl gld 63mm 1 Pt Kt	1
ACW75S-LSF	Brass cbl gld 75mm 1 Pt Kt	1
ACW75-LSF	Brass cbl gld 75mm 1 Pt Kt	1