

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [88768-5200](#)
Status: **Active**
Overview: [DMS-59®](#)
Description: 1.27mm Pitch DMS-59®-to-Two VGA Adapters Cable Assembly, 0.20m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-88768-5200 \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88759
Assembly Configuration	Dual Ended Connectors
Connector to Connector	DMS-59™-to-VGA
Overview	DMS-59®
Product Name	DMS59®
UPC	756054581315

Physical

Cable Length	0.20m
Circuits (Loaded)	59
Color - Resin	Black
Gender	Male-Female
Lock to Mating Part	Yes
Material - Metal	Aluminum, Phosphor Bronze
Material - Plating Mating	Gold, N/A
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Low Density Polyethylene
Net Weight	122.300/g
Packaging Type	Bag
Pitch - Mating Interface	1.27mm
Plating min - Mating	1.905µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	N/A, Through Hole
Wire Insulation Diameter	N/A
Wire Size AWG	32
Wire/Cable Type	Round


Electrical

Current - Maximum per Contact	1A
Impedance	75#
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

Reference - Drawing Numbers

Product Specification	PS-88768-5200
Sales Drawing	SD-88744-096



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[88759Series](#)