

RJ45 socket insert - CUC-V04-BU-180 - 1407409

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




RJ45 socket insert, 1-way, for PCB mounting, CAT5e, 8-pos., shielded, with straight solder pins (THT)



Ethernet

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 772297
Weight per Piece (excluding packing)	6.1 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABNADD
Note	Made to Order (non-returnable)

Technical data

Mechanical characteristics

Standards/specifications	IEC 60603-7
Number of positions	8
Connection profile	RJ45 8(8)
Insertion/withdrawal cycles	≥ 750
Connection method	Solder connection

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Housing material	Copper alloy

Electrical characteristics

RJ45 socket insert - CUC-V04-BU-180 - 1407409

Technical data

Electrical characteristics

Number of positions	8
Nominal voltage U_N	50 V
Nominal current I_N	1.5 A

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Accessories

Panel mounting frame

Panel mounting frames - CUC-V04-F-POBK-180 - 1407410



Panel mounting frames, Degree of protection: IP65/67, Material: Plastic