



FGN.2M.312.XLCM

MECHANICAL DETAILS

Shell Style Model FG* : Straight plug with arctic grip and MIL spec backend

Keying 3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)

Housing Material Environment friendly aluminium (nickel plated, anthracite color) shell and nut, other pieces bronze/brass

Cable Fixing 0 - 0 mm

Variant 2 :

				A	B	C	D	F
Mm.				18.9	14.0	17.2	13.0	15.5
In.				0.74	0.55	0.68	0.51	0.61

PERFORMANCE DETAIL

Insert 2M.312 : 12 Low Voltage

Insulator

Specifications

Contact Type: Crimp

Max. Matings: 5000

Contact 22 N

Contact Dia.: 0.7 mm (0.028in)

Bucket Dia.: 0.8 mm (0.031in)

Min. Conductor: 0.14 mm² (AWG 26)

Max. Conductor: 0.34 mm² (AWG 22)

R (max): 6.1 mOhm

Extractor: DCF.93.070.4LT

Positioner: DCE.91.070.5MVC

OTHER CHARACTERISTICS

Shell Style/Model Libellé

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]



Operating -55°C/ +200°C

Climatical 15/200/21 (Al. shell)

Lighting strike EIA 10K amps - 6 times

EMI Shielding EIA - 1Ghz-80 dB,3GHz-70 dB,6GHz- 58dB

IP Rating 68





FGN.2M.312.XLCM

Available Download

 [M_series.pdf](#)

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)