


LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
			A	NEW RELEASE/RTS 106102	08/APR/08	ECC JDM



1. CABLE: 3XRG174 FLAT, GROOVED
2. MATERIAL/PARTS WHICH CONTAIN THE PROHIBITED SUBSTANCE
[CLASSIFICATION OF ENVIRONMENT RELATED SUBSTANCE,(1) CLASS I
SUBSTANCE FOR 4.2 (PROHIBITED TO USE),ANNEXED TABLE 1] OF
ENVIRONMENT RELATED SUBSTANCE CONTROL STANDARD (14-2.5.06)
MUST NOT USE IN PRODUCT AND MANUFACTURING PROCESS.
3. CADMIUM CONTENT: 5PPM UNDER(ONLY PLASTIC/RUBBER)
4. ASSEMBLE PER 114-13098
5. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TYCO ELECTRONICS ELECTRICAL STANDARD 230-702 ("ROHS")

222.0±20.0	2053075-3
1500.0±20.0	2053075-2
800.0±20.0	2053075-1
"L"	TYCO ELECTRONICS P/N

A/R	A/R	A/R	FT	3C-RG174 COAXIAL CABLE	7
3	3	3	PC	SHIELD CONTACT	6
3	3	3	PC	CENTER CONTACT	5
3	3	3	PC	INSULATOR	4
1	1	1	PC	HOUSING, OUTER W/ FLANGES, KEYED	3
1	1	1	PC	INTERMOLD	2
1	1	1	PC	BOOT, OUTER W/ FLANGES	1
-3	-2	-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.2

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
E.C. CLAYBAUGH
08/APR/08

CHK
J.D. MONTGOMERY
08/APR/08

APVD
J.D. MONTGOMERY
08/APR/08

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
CABLE ASSY, QSL, 3 PORT W/FLANGE, PIGTAIL

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2053075

RESTRICTED TO
-

SCALE
N.T.S.

SHEET
1 OF 1

REV
A