

# CyMotion Master Solar M86-21950 **CyMotion Line**



Solar - wireless keyboard with energy-saving wireless optical mouse

## **Key benefits**

- ADVANCED TECHNOLOGY KEYBOARD for even better key operation (ATK)
- High transmission and anti-tapping . security thanks to data encryption with "Cherry Security Radio Technology"
- . No working interruptions - no change of batteries - no recharging due to solar cell in the keyboard
- Optional battery recharge during operation
- Precise working with the optical mouse due to the high resolution of 800 dpi
- Elegant, symmetric design
- Quick access to frequently-used functions with the unique, sidemounted Xpress-keys (freelyprogrammable)
- 19 additional, free-programmable keys for controlling multimedia, Internet and your own applications
- Extra @-key and key for currency function
- . Individual and easy key assignment due to our KeyM@n Software with new, comfort functions
- . Palm rest with unique space saving storage feature
- Navigation of the mouse pointer with cursor keys

## **Delivery volume**

Wireless keyboard Wireless optical mouse Wrist rest Receiver Charging cable for mouse 4x rechargeable Alkali batteries Adapter USB-PS/2 CD-ROM Printed manual

# Approvals

FCC, cUR/cURus, CE, c-tick, GHOST-R Microsoft Windows ™ ME, 2000, XP

## System requirements

USB or PS/2 interface

# **Technical data**

### Number of keys:

104 + 29 = US layout with Windows <sup>™</sup> and additional kevs 105 + 29 = EU layout with Windows <sup>™</sup> and additional keys

## Weight:

approx. 1190 g (keyboard) approx. 2210 g (bundle)

#### **Dimensions:**

approx. 495 x 195 x 37 mm (keyboard) approx. 560 x 325 x 65 mm (packaging)

Range of coverage: typ. 2 m

Storage temperature: -20 °C until 60 °C

#### Working temperature: 0 °C until 50 °C

Operating life of standard single key: >20 million operations



Interface:

1x USB and 2x PS/2

#### **Current input:**

Keyboard: typ. 6 mA (at 2,0-3,3 V) Mouse: typ. 20 mA (at 2,0-3,3 V) Receiver: typ. 10 mA (at 4,0-5,25 V)

#### Packaging unit:

29 keyboards per master carton 2 master cartons per pallet

#### **Guarantee period:**

2 years

## **Order description**

Order number	0	Number of keys
M86-21950xxAAAAC	silver/black	133/134

The xx in the order description defines the country version.

- ΒE Belgium
- СН Switzerland
- DE Germany
- ES Spain
- EU US English/ international with €
- FR France
- GB English (UK)
- IT Italy
- SF Sweden/ Finland
- SL Slovenia RG
- Russia

Country version upon request.

Cherry GmbH Cherrystraße D-91275 Auerbach/Opf. Phone: +49 (0) 9643 18-0 Hotline: +49 (0) 9643 18-206 +49 (0) 9643 18-1545 Fax: Internet: www.cherry.de

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relate to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding. © 2003 Cherry GmbH