## **INTERFACE MODULES & SUPPORTS**

## Male and Female D-Connector Interface Modules

- D Sub male and female to screw terminals
- Terminals marked 1 2 3 etc (+ Shield)
- Separate shield connection
- 35mm DIN rail mounting
- Option for 32mm (G) rail mounting
- Available with optional wall mounting plates
- 45° terminals for easy access
- · RoHS compliant
- SVHC free (2012)

CIM/XXW-DMFS	SPECIFICATION			
	Rating	50V DC 100mA		
	Cable entry	0.2-4mm² (30-12 AWG)		
	Terminal screw	M3		
	Strip length	6mm (0.24")		
	Max terminal torque	0.5Nm (4lb-in)		
	Dimensions:	Height:	Width:	Length:
	CIM/9W-DMFS	39mm (1.54")	83mm (3.27")	35mm (1.38")
	CIM/15W-DMFS	39mm (1.54")	83mm (3.27")	58mm (2.28")
	CIM/25W-DMFS	39mm (1.54")	83mm (3.27")	78mm (3.07")
	CIM/37W-DMFS	39mm (1.54")	83mm (3.27")	114mm (4.49°)
	CIM/50W-DMFS	37mm (1.46")	83mm (3.27')	136mm (5.36°)

TYPE NO.	DESCRIPTION
CIM/9W-DMFS	9 way male and female D Sub screw terminal interface. 35 mm din rail mounting
CIM/15W-DMFS	15 way male and female D Sub screw terminal interface. 35 mm din rail mounting
CIM/25W-DMFS	25 way male and female D Sub screw terminal interface. 35 mm din rail mounting
CIM/37W-DMFS	37 way male and female D Sub screw terminal interface. 35 mm din rail mounting
CIM/50W-DMFS	50 way male and female D Sub screw terminal interface. 35 mm din rail mounting

PCB TERMINAL BLOCKS

INTER-CONNECTION

> FUSES & FUSE-HOLDERS

LEDs & INDICATORS

MINIATURE SWITCHES

LIMIT & SAFETY SWITCHES

CONTROL PRODUCTS

INTERFACE MODULES & SUPPORTS

> RELAY BASES

**ENCLOSURES** 

**BATTERIES** 

TRANS-FORMERS