

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

08-58-0125

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 396 Crimp Terminal 2578, 22-26 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au)



Series

image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Specification PS-08-50 \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	2578
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Packaging Alternative	08-58-0126 (Loose)
Product Name	KK® 396
UPC	800754227025

Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

Material Info	
Old Part Number	2578-B-(550)

Reference - Drawing Numbers	
Product Specification	PS-08-50
Sales Drawing	SD-2578

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2578Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 , 5239

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for Crimp Terminals	0638117400
Extraction Tool	0011030016
Terminator Die	0011402097
Terminator Die	0011402099
Mini-Mac™	0638881000
Applicator	

This document was generated on 12/16/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION