



PERFORMANCE DETAIL

Insert 1M.308 : 8 Low Voltage

Insulator

Specifications

Contact Type: Print (straight)

Max. Matings: 5000

Contact Dia.: 0.7 mm (0.028in)

R (max): 6.1 mOhm



OTHER CHARACTERISTICS

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]

Operating -20°C/ +80°C

Climatical 15/200/21 (Al. shell)

Lighting strike EIA 10K amps - 6 times

EMI Shielding EIA - 1Ghz-80 dB,3GHz-70 dB,6GHz- 58dB

IP Rating 68

