

Han D HMC female contact Au AWG 26-22



Part number: 09 15 200 6224

Description: Han D HMC female contact Au AWG 26-22

Features	
Gender:	female
RoHS conformity:	Yes
Type of contact:	Crimp contact
Series:	Han D® HMC
Connection data	
Contact resistance:	$\leq 3 \text{ m}\Omega$
Stripping length:	8 mm
Wire gauge mm ² min.:	0.14 mm ²
Wire gauge, max.:	0.37 mm ²
Wire gauge AWG, min.:	AWG 26
Wire gauge AWG, max.:	AWG 22
Material properties	
Material, contact:	copper alloy
Surface, contacts:	HMC gold plated contacts
Dimensions and weight	
Net Weight:	0.69 g
Norms and specifications	
Specification:	DIN EN 60 664-1DIN EN 61 984
Supplementals	
Diameter of drilling hole:	0.9 mm