



SIDE:A




ITEM NO	CS28102	CS28103
L (mm)	1000	1800
±T (mm)	±10	±20

SIDE:B



<u>SIDE:A</u>		<u>SIDE:B</u>
USB CM		USB AM
A4+B4+A9+B9	red	1
A6	white	3
A7	green	2
A1+B1+A12+B12	black	4+7
A2	blue	6
A3	yellow	5
A1+B1+A12+B12	drain	4+7
B10	orange	8
B11	purple	9
A1+B1+A12+B12	drain	4+7
Shell	braid	Shell

PIN OUT



PE PACKING

NOTE:

- Mold:Type-C:JL-MD638、MD639 USBAM: JL-MD640
- 100% electrical performance test
Parameter Settings: CT-8681FA
a. Insulation Resistance:5MΩ (MIN).
b. Conductive Resistance:2.0Ω (MAX).
- Packing: PE Packing+Label

0		2014. 12. 25	14500
REV	DESCRIPTION	DATE	NOTE

UNIT:mm	TITLE: USB3.1 Cable Assembly (USB3.1 CM/AM Black)		
SCALE	P/N: CS28102 CS28103		
UNLESS OTHERWISE SPECIFIED TOLERANCES: X ± X XX ± XX XXX ± XXX ANGLE ±			DR:LDF
REV.:0	SHEET:4/4	DWG. NO:JL-2147D	CH:
			AP: