



Splice Connector

T&B Catalog Number:

UPC Number:

Status:

Description:

D8-PS-D

78621089076

Active

Non-Insulated Parallel Splice Connector For Wire Range 8 For Circular Mil Range 13,100-20,800 Length .375 Diameter .26,Metallic

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Resistant to corrosion and preserve the electrical integrity of the wires in single or multiple strands. Feature an intelligent constructable part number for quick identification of the wire range.

General

Insulation Type	Non-Insulated
Terminal Series	D
Material	Copper
Finish	Tin Plated
Color	Metallic
Wire Range	8

Dimension Information

A (inches)	.375
B (inches)	.260
C (inches)	.180

Specifications

Circular Mil Area	13,100-20,800
Voltage Rating	600V

Tooling

Tool Charts	Available on Website
Application Tools	ERG4005, WT115A, TBM8750M1, TBM8750BSCR
Recommended Tool	ERG4005, WT115A

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.37 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000229
Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com