



Ferrule

T&B Catalog Number:

F9000

UPC Number:

78621098258

Status:

Active

Description:

Non-Insulated Ferrule for Wire Size 24, Wire Size 0.25 mm², Length 0.196 inches, Metallic

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.



General

Ferrule Type	Uninsulated
Insulation Type	Non-Insulated
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	24
Wire Size (mm ²)	.25

Dimension Information

A (mm)	5.0
Diameter C (inches)	.030
Diameter C (mm)	0.8
Diameter D (inches)	.067
Diameter D (mm)	1.7
E (mm)	.15
A (inches)	.196
E (inches)	.006

Specifications

Temperature Rating	150°C
Voltage Rating	300V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	T1, ERG2
Recommended Tool	T1, T3, ERG4

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	20000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.06 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000319
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Ferrule dimensions conform to DIN 46228, Part 4.

Certifications

RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com