



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

CC-PG7-G

UPC Number:

78621021160

Status:

Active

Description:

Non-metallic gray nylon cable gland with PG threads, cord range-.118-.256; thread length-.315.

Features

Sturdy cable sealing mechanism which results in superior strain relief.

Compact size ensures quick and easy installation in cramped spaces

Non-metallic construction provides excellent corrosion, chemical and impact resistance.

General

Material Nylon

Color Gray

Dimension Information

Thread Length (inches) 0.315

Cord Range (inches) .118-.256

Thread Size (PG) 7

Thread Length (mm) 8

Specifications

3dmodel Available on Website

Temperature Rating -30 C (-86F) to +80 (176F) - continuous

Accessories & Components

Locknut Catalog Nbr LN-PG7-G

Packaging

T&B Inner Pack 50

Package in Units 200

T&B Sold in UOM Each

T&B Weight Per UOM 2.5 lbs. per 1000

Application Support

T&B Sales Drawings wsd-000004

T&B Instruction Sheets ta02021-tb2

Product Overview Available on Website

Portable Cord Selection Table Available on Website

Notes

Working temperatures- -30° C (-86F) to +80° (176F)

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com