

## 18U SmartRack Deep Rack Enclosure Cabinet

MODEL NUMBER: **SR18UB**



### Description

Tripp Lite's SR18UB premium SmartRack 18U Enclosure Cabinet is packed with features designed to simplify rack equipment installations and rack equipment maintenance: top and bottom cable routing ports, perforated door and side panels to promote efficient airflow, adjustable vertical mounting rails and more. And as part of the SmartRack family, the SR18UB is compatible with Tripp Lite's extensive range of rackmount accessories, enabling you to customize your solution to meet any requirement. The SR18UB ships fully assembled for quick installation and comes with a 5-year warranty.

The SR18UB is compatible with all standard 19-inch rack equipment and features front and rear pairs of vertical rails with square mounting holes. The rails are adjustable in quarter-inch increments to accommodate equipment depths from 3 to 32.5 inches, ideal for standard server installation. Adjustment is quick and convenient: simply unscrew the rails, slide them to the desired depth and restore the screws. The rails feature square mounting holes and are capable of supporting up to 1,000 lbs of equipment with included installation hardware. Each rack space within the enclosure is numbered for easy reference.

With a locking, reversible front door and locking, removable side panels, the SR18UB provides safe, secure installation for all equipment. This prevents unauthorized access to installed equipment while making it easy for authorized personnel to perform inspections, maintenance and equipment replacement. The enclosure meets all requirements toward PCI DSS compliance.

The top and bottom panels of the SR18UB are furnished with vents designed to help remove warm air from the enclosure and draw in cool air by convection. They also support installation of standard user-supplied case fans (Tripp Lite SRFANWM). The top and bottom panels are also provided with ports for cable routing.

To simplify deployment, the SR18UB comes with an accessory caster kit consisting of 4 casters and all required installation hardware. With casters installed, the SR18UB can easily be maneuvered into to desired location, and then secured in place by adjusting the unit's levelers. Note: the casters are intended for minor position adjustments within the final installation area only and are not designed for moving the enclosure over long distances.

### Features

- 18U extra deep enclosure

### Highlights

- 18U with adjustable front and rear vertical rackmount rails
- Extended depth of 33" allow for standard server installation
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Casters and leveling feet
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) compliance

### Package Includes

- SR18UB Rack Enclosure
- (42) M6 screws
- (42) M6 cage nuts
- (42) M6 washers
- (4) Casters
- (4) Levelers
- (2) keys
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Adjustable mounting depths from 3" to 32.5" inches
- Locking, reversible front door
- Locking, removable side panels
- Top and bottom panel cable access openings
- Fully assembled for quick installation
- Casters and leveling feet
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) compliance

## Specifications

SELECTOR	
Selector Type	RACK EQUIPMENT
General Info	
Product Group	RACKS
TAA Compliant	No
OVERVIEW	
Style	Floor Standing
Rack Type	Floor-Standing
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	32.5
Installed Whole System Maximum Rack Depth (cm)	82.6
Installed Whole System Minimum Rack Depth (in.)	3
Installed Whole System Minimum Rack Depth (cm)	7.62
Rack Height (U Spaces)	18
Shipping Dimensions (hwd / in.)	41.61 x 25.6 x 35.03
Shipping Weight (lbs.)	123
Unit Dimensions (hwd / in.)	35.6 x 23.63 x 33.5
Unit Weight (lbs.)	105
Color	Black
Weight Capacity - Stationary (lbs.)	1,000
Weight Capacity - Rolling (lbs.)	1,000
Factory Preset Rack Depth (in.)	28.31



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Factory Preset Rack Depth (cm)	71.91
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
<b>SPECIAL FEATURES</b>	
Grounding Lug	Front and Back door frames
<b>CERTIFICATIONS</b>	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	UL60950; RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.