



Based LED type	MultiLED
Size (inch)	T-3 1/4
Size (mm)	T10
Housing size	10x28mm
Base	BA9s
Chip number	8
Chip color	red
Wavelength (nm)	620
Op. voltage (V)	24
Rectifier	Bridge
AC current	16
DC current	16
Type Iv DC current	110
Voltage tolerance (%)	10%
Op. temperature (°C)	-20°C...+60°C
Storage temperature (°C)	-25°C...+80°C

Drawn : DIL	Ch'd : DIL	Datasheet : 18310	Print date : 27/04/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :