



Based LED type	MultiLED
Size (inch)	T-1 3/4
Size (mm)	T6
Housing size	6.1x15.9mm
Base	MG
Chip number	6
Chip color	green
Wavelength (nm)	567
Op. voltage (V)	28
Rectifier	Protection Diode
AC current	-
DC current	14
Type Iv DC current	84
Voltage tolerance (%)	10%
Op. temperature (°C)	-20°C...+60°C
Storage temperature (°C)	-25°C...+80°C

Drawn : DIL	Ch'd : DIL	Datasheet : 15121M	Print date : 27/04/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :