



<b>Based LED type</b>	MultiLED
<b>Size (inch)</b>	T-1 3/4
<b>Size (mm)</b>	T6
<b>Housing size</b>	6.1x15.9mm
<b>Base</b>	MG
<b>Chip number</b>	6
<b>Chip color</b>	green
<b>Wavelength (nm)</b>	567
<b>Op. voltage (V)</b>	24
<b>Rectifier</b>	Protection Diode
<b>AC current</b>	-
<b>DC current</b>	14
<b>Type I<sub>v</sub> DC current</b>	84
<b>Voltage tolerance (%)</b>	10%
<b>Op. temperature (°C)</b>	-20°C...+60°C
<b>Storage temperature (°C)</b>	-25°C...+80°C

Drawn : DIL	Ch'd : DIL	Datasheet : 15121M	Print date : 27/04/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :