

BOB™ LED



FEATURES

- Simulated flame effect with no heat
- Continuous operation (no duty cycle)
- Includes 3 legs for table support and chain for suspension

SPECIFICATIONS

- Light source: 66 (54 orange, 12 blue) LEDs
- Power and current: 120V, 60Hz: 33W, 0.3A operating, 0.3A inrush
- AC power: 115V/60Hz or 230V/50Hz
- Weight (with legs): 5.1lbs (2.3kg)
- Weight (with chain): 4.8lbs (2.2kg)
- Size (with legs): 14in x 14in x 31in
356mm x 356mm x 787mm
- Size (with chain): 12in x 12in x 30in
305mm x 305mm x 762mm

www.chauvetlighting.com
info@chauvetlighting.com
t: 954.929.1115
3000 North 29th Court
Hollywood, FL 33020

CHAUVET
Value • Innovation • Performance