

## Classic Globe (GLS) Omni-Lamp 4.6W (40W) 3000K 470lm B22 Non-Dimmable 330 deg Beam Angle

Quick Order Code: 39-37-74 / Page: 1



This cutting edge A++, 4.6W retro-fit Integral LED Classic Globe (GLS) (frosted finish, large bayonet base) from the Omni-Lamp range delivers a warm white light and brightness, similar to a 40W filament bulb. It has the appearance, feel and weight of a traditional light bulb. Featuring a ceramic filament COB LED chip, which enables a super-wide 330 degree beam angle. Finished in an aluminium and plastic, thermally efficient body. Ideal for living rooms, hallways and kitchens.

### Product Details

Partcode: ILA60B22O4.6N03KHEWA

Quick Order Code: 39-37-74

Range Name: Omni

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Classic Globe (GLS)

Warranty: 2 Years

CE / RoHS: Yes

### Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Plastic, Aluminium, Glass, Nickel plated brass

Construction: Plastic and Aluminium heat sink, glass diffuser

**Physical Data**

Length: 105mm  
Width: 60mm  
Weight (Unpackaged Single Unit): 41g  
Lamp or Luminaire Shape: Round  
Lamp Fixing: Pendant

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 4.6 Watts  
Driver included: Yes  
Electric Current: AC  
Ampage: 52.00mA  
Frequency Range: 50/60 Hz  
Power Factor:  $\geq 0.40$   
Wattage Equivalent: 40 Watts  
Dimming: Non-dimmable  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 470lm  
Lumens per Watt: 102.2lm/W  
Beam Angle: 330°  
Correlated Colour Temperature (CCT): 3,000k  
Colour Temperature: Warm White  
Colour Rendering Index (CRI):  $\geq 80$   
LED Type: Filament ceramic COB chip  
Instant on - Less than 1 second: Yes  
Lifetime: 15,000 hrs  
Switching Cycles:  $>7,500$  X

### Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788204268

Packaged Weight (Unit of 1): 99g

Length (unit of 1): 135mm

Width (unit of 1): 70mm

Depth (unit of 1): 70mm

**Outer packaging info available on website**

*Product data last updated on: Tuesday, September 23, 2014 - 15:28*