

**Classic Globe (GLS) 12W (75W) 2700K 1060lm B22 Non-Dimmable Frosted Lamp**

*Quick Order Code: 20-73-78 / Page: 1*

**Product Details**

Partcode: ILA60B22O12N27KBKWA

Quick Order Code: 20-73-78

Range Name: Mensae

Product Type: Classic Globe (GLS)

Warranty: 3 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Aluminium, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

**Physical Data**

Length: 125mm  
Width: 60mm  
Weight (Unpackaged Single Unit): 148g  
Lamp or Luminaire Shape: Round

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 12.0 Watts  
Driver included: Yes  
Driver IC Manufacturer: Silergy  
Electric Current: AC  
Ampage: 104.00mA  
Frequency Range: 50 Hz  
Power Factor:  $\geq 0.50$   
Wattage Equivalent: 75 Watts  
Dimming: Non-dimmable  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 1,060lm  
Lumens per Watt: 88.0lm/W  
Beam Angle: 240°  
Correlated Colour Temperature (CCT): 2,700k  
Colour Temperature: Warm  
Colour Rendering Index (CRI):  $\geq 80$   
LED Manufacturer: Everlight  
LED Type: Surface mounted device (SMD)  
Instant on - Less than 1 second: Yes  
Lifetime: 25,000 hrs  
Switching Cycles: >12,500 X

Quick Order Code: 20-73-78 / Page: 3

### Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788208815

Packaged Weight (Unit of 1): 188g

Length (unit of 1): 140mm

Width (unit of 1): 68mm

Depth (unit of 1): 68mm

**Outer packaging info available on website**

*Product data last updated on: Friday, October 3, 2014 - 13:27*