



DISTRIBUTION BOARD

AK 09



AK 09

Distribution board

CUSTOMIZABLE

200 x 200 x 122 mm
Article number: 73540901

Distribution board, 9 modules, PE/N terminal, with each 2 clamping points 16 mm², 5 clamping points 6 mm², 6 elastic entries on top, masking and labelling strips, insulating seals, additional double-membrane seals



Technical data

Measures

Width:	200 mm
Length:	200 mm
Height:	122 mm

Material

Base:	Polystyrene, grey, similar to RAL 7035
Cover:	Polystyrene, grey, similar to RAL 7035
Sealing:	Polyurethane
Cover screw:	Polyamide 6, fiber-glass reinforced

Accessory

- AK SGA-1 - Lock fittings
- AK AS - Masking-off strips
- BST M20 - Ventilation seal

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%



DISTRIBUTION BOARD

AK 09

Other attributes

Color:	grey
Ingress protection:	IP65 - acc. EN 60529 / DIN VDE 0470-1
Number of distribution units:	9
Tackable:	Yes
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
sealable:	Yes