


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39544-3003](#)
Status: **Active**
Overview: [Eurostyle™ Terminal Blocks](#)
Description: 5.08mm Pitch Eurostyle™ Vertical Fixed Mount PCB Terminal Block, 3 Circuits



Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	39544
Application	N/A
Component Type	One Piece
MolexKits	Yes
Overview	Eurostyle™ Terminal Blocks
Product Name	ESE, Eurostyle™Fixed Mount
Type	Euro Block
UPC	822350546997

Physical

Circuits (Loaded)	3
Entry Angle	Horizontal
Lock to Mating Part	None
Net Weight	4.280/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.00mm
PCB Thickness - Recommended	2.00mm
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22
Wire Size mm²	0.33 - 3.31

Electrical

Current - Maximum per Contact	15A
Voltage - Maximum	300V

Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	135
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-39544-001
---------------	--------------

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[39544Series](#)