



3M™ Organic Vapor Cartridge/Filter 60921, P100 Respiratory Protection 60/Case

3M ID 70070614485 UPC# 50051138464658 3M Product Number 60921 CAT# 60921

NIOSH approved against certain organic vapors and particulates. Use with 3M™ Half and Full Facepieces 6000, 7000 and FF-400 Series with bayonet filter holders.

- Combined Organic vapor cartridge with P100 particulate filter
- Swept-back design for enhanced field of view and balance
- Use with 3M™ Reusable Respirators



This organic vapor cartridge/P100 filter can be used for a variety of applications, including petrochemical and chemical

processing, utilities, pharmaceuticals, mining and primary metals. Swept-back design offers enhanced comfort and visibility.

- When properly fitted, helps provide respiratory protection from certain organic vapors as well as non-oil and oil particulates at concentrations up to 10 times the Permissible Exposure Limit (PEL) with half facepieces or 50 times PEL with full facepieces.
- Full facepieces must be quantitatively fit tested to claim assigned protection factor above 10 in negative pressure mode.
- Not for use in environments that are immediately dangerous to life or health (IDLH).

Specifications

Gas & Vapor Protection Type	Organic Vapor
Height	3.4 Inch
Length	4.2 Inch
National Stock Number	4240-01-455-7353

NIOSH Cartridge or Filter Assigned Color Coding Magenta/Black

Nuisance Odor Relief (< OSHA PEL) N/A

Recommended Application Chemical Clean-up, Chemical Compounding, Chemical Transfer, Laboratories, Pesticide Application

Recommended Industry Construction, General Manufacturing, Mining, Oil & Gas, Transportation

Standards/Approvals Organic Vapors, P100

US Govt Contract Number GS-07F-0374J