

# MAX520S.079



DIM ESTERNE / EXTERNAL DIM.:	574 x 361 x H225 mm 22.60 x 14.21 x H8.86 inch.
DIM INTERNE / INTERNAL DIM.:	520 x 290 x H200 mm 20.47x 11.42 x H7.87 inch.
PROFONDITÀ COPERCHIO-FONDO / LID-BOTTOM DEPTH:	45 + 155 mm 1.77 + 6.10 inch.
PESO / WEIGHT:	4100 g
COLORI / COLORS:	■
CARATTERISTICHE / FEATURES:	IP67 spugne cubettate / cubed foams

# MAX520STR.079



975 mm  
38.39 inch

DIM ESTERNE / EXTERNAL DIM.:	585 x 361 x H238 mm 23.03 x 14.21 x H9.37 inch.
DIM INTERNE / INTERNAL DIM.:	520 x 290 x H200 mm 20.47x 11.42 x H7.87 inch.
PROFONDITÀ COPERCHIO-FONDO / LID-BOTTOM DEPTH:	45 + 155 mm 1.77 + 6.10 inch.
PESO / WEIGHT:	5800 g
COLORI / COLORS:	■
CARATTERISTICHE / FEATURES:	ruote / wheels maniglia telescopica / extendable handle IP67 spugne cubettate / cubed foams

**MANIGLIA LATERALE SU ENTRAMBI I LATI**  
SIDE HANDLES

**RUOTE CON ASSALE IN ACCIAIO INOX**  
WHEELS WITH STAINLESS STEEL PIN  
**RETRO MANIGLIA TELESCOPICA A SCOMPARSA**  
EXTENDABLE HANDLE