

MAX540H190S.079

NEW



DIM ESTERNE / EXTERNAL DIM.:	594 x 473 x H215 mm 23.39 x 18.62 x H8.46 inch.
DIM INTERNE / INTERNAL DIM.:	538 x 405 x H190 mm 21.18 x 15.94 x H7.48 inch.
PROFONDITÀ COPERCHIO-FONDO / LID-BOTTOM DEPTH:	50 + 140 mm 1.97+ 5.51 inch.
PESO / WEIGHT:	4900 g
COLORI / COLORS:	■
CARATTERISTICHE / FEATURES:	IP67 spugne cubettate / cubed foams

MANIGLIA LATERALE SU ENTRAMBI I LATI

SIDE HANDLES

MAX540H190STR.079

NEW



980 mm
38.58 inch

DIM ESTERNE / EXTERNAL DIM.:	604 x 473 x H225 mm 23.78x 18.62 x H8.86 inch.
DIM INTERNE / INTERNAL DIM.:	538 x 405 x H190 mm 21.18 x 15.94 x H7.48 inch.
PROFONDITÀ COPERCHIO-FONDO / LID-BOTTOM DEPTH:	50 + 140 mm 1.97 + 5.51 inch.
PESO / WEIGHT:	6600 g
COLORI / COLORS:	■
CARATTERISTICHE / FEATURES:	ruote / wheels maniglia telescopica / extendable handle IP67 spugne cubettate / cubed foams

MANIGLIA LATERALE SU ENTRAMBI I LATI

SIDE HANDLES

RUOTE CON ASSALE IN ACCIAIO INOX

WHEELS WITH STAINLESS STEEL PIN

RETRO MANIGLIA TELESCOPICA A SCOMPARSA

EXTENDABLE HANDLE