

MAX540 H245

NEW



| | |
|---|---|
| DIM ESTERNE / EXTERNAL DIM.: | 594 x 473 x H270 mm 23.39 x 18.62 x H10.63 inch. |
| DIM INTERNE / INTERNAL DIM.: | 538 x 405 x H245 mm 21.18 x 15.94 x H9.64 inch. |
| PROFONDITÀ COPERCHIO-FONDO / LID-BOTTOM DEPTH: | 50 + 195 mm 1.97 + 7.68 inch. |
| PESO / WEIGHT: | 5300 g |
| COLORI / COLORS: | ■ |
| CARATTERISTICHE / FEATURES: | IP67 |
| ACCESSORI / ACCESSORIES: | spugne cubettate / cubed foams |

MANIGLIA LATERALE SU ENTRAMBI I LATI

SIDE HANDLES

MAX540 H245 TR

NEW



980 mm
38.58 inch

| | |
|---|--|
| DIM ESTERNE / EXTERNAL DIM.: | 604 x 473 x H283 mm 23.78 x 18.62 x H11.14 inch. |
| DIM INTERNE / INTERNAL DIM.: | 538 x 405 x H245 mm 21.18 x 15.94 x H9.64 inch. |
| PROFONDITÀ COPERCHIO-FONDO / LID-BOTTOM DEPTH: | 50 + 195 mm 1.97 + 7.68 inch. |
| PESO / WEIGHT: | 7000 g |
| COLORI / COLORS: | ■ |
| CARATTERISTICHE / FEATURES: | ruote / wheels maniglia telescopica / extendable handle IP67 |
| ACCESSORI / ACCESSORIES: | spugne cubettate / cubed foams |

MANIGLIA LATERALE SU ENTRAMBI I LATI

SIDE HANDLES

RUOTE CON ASSALE IN ACCIAIO INOX

WHEELS WITH STAINLESS STEEL PIN

RETRO-MANIGLIA TELESCOPICA A SCOMPARSA

EXTENDABLE HANDLE