

Product specifications

Materials	
body	aluminum alloy
lens	polycarbonate, UL rating 94-V2
washer	steel, zinc plated
retaining nut	aluminum alloy
fiber optic	1.5mm optical core, 2.2mm polyethylene cable jacket
moisture seal	EPDM

Installation specification	
mounting hole	.400±.004 (10.1mm±.1)
panel thickness	.059 (1.5mm) min to .320 (8.1mm) max

Ordering data

FLXR Litepipe™
ordering code (example)

FLXR X XXX XX

